

Basket Handling Elevator (BHE)

Vertical Lift



Manufactured in the USA by:



Please Call for a Price Quote: (847) 640-8923

- NESHAP Compliant Features
 Minimizes worker vapor exposure and reduces contact with the solvent.
- Enhanced Solvent Containment
 Horizontal slide lid can be closed when parts are being processed for increased solvent containment.
- Labor Cost Savings
 Reduces or eliminates operator processing time.
- Processing Consistency
 Ensures parts are processed consistently to your specification.
- 20 Part Cleaning Recipes
 Touch-Screen PLC allows you to enter, save & easily select between 20 different part recipes.
- Minimized Solvent Losses
 PLC controlled movement combined with sufficient time in the refrigerated flash-off zone while processing with the lid closed greatly reduces solvent losses compared to manual processing.
- Automated Operation
 Reduces operator error and increases productivity.
- Process Basket with Lid Closed
 Ensures solvent containment through entire cycle.

RELSPEC.com



Handling Elevator

Vertical over Ultrasonic Immersion Sump
20 Recipes
25 lbs. including part basket (1212LE) 35 lbs. including part basket (2012LE)
10"L x 10"W x 4" Deep (1212LE) 17"L x 10"W x 4" Deep (2012LE)
PLC Touchscreen Controlled
Allows for manual operation of the BHE Lift
Automatically processes the part basket according to the cleaning recipe selected by operator
System allows for the operator selection as between any of the 20 recipes that you created.
Cleaning recipes are easily stored in a password- protected menu. The operator cannot change the con- tent of a recipe
Pneumatic slide with easily adjustable magnetic reed switch positioning.
Includes light pendant to advise of the state of the BHE Lift including ready, in cycle, cycle complete and fault error.
Part baskets are processed through the cleaning cycle with the lid closed for enhanced solvent containment.
•







Please Call for a Price Quote (847) 640-8923